



1a



1b



e.sybox

QUICK GUIDE








- UK** DAB PUMPS LTD. Units 4 and 5, Startford Hall Industrial Park, Dunmow Road, Bishops Startford, Herts CM23 5EZ - UK salesuk@dwgroup.com Tel.: +44 1279 652 776 Fax: +44 1279 57 727
- Spain** DAB PUMPS IBERICA S.L. Avenida de Castilla nr.1 Local 14 28830 - San Fernando De Henares - Madrid Spain info.spain@dwgroup.com Ph.: +34 91 6569545 Fax: +34 91 6569676
- Belgium** DAB PUMPS B.V. Brusselstraat 150 B-1702 Groot-Bijgaarden - Belgium info.belgium@dwgroup.com Tel.: +32 2 4668353 Fax: +32 2 4669218
- Netherlands** DAB PUMPS B.V. Albert Einsteinweg, 4 5151 DL Drunen - Nederland info.nl@dwgroup.com Tel.: +31 416 387280 Fax: +31 416 387299
- USA** DAB PUMPS INC. 3226 Benchmark Drive Ladson, SC 29456 USA info.usa@dwgroup.com Ph.: 1-843-824-6332 Toll Free: 1-866-896-4DAB (4322) Fax: 1-843-797-3366
- South Africa** DWT South Africa Podium at Menlyn, 3rd Floor, Unit 3001b, 43 Ingersol Road, C/O Lois and Atterbury, Menlyn, Pretoria, 0181 South-Africa info.sa@dwgroup.com Tel: +27 12 361 3997 Fax +27 12 361 3137
- Russia** OOO DAB PUMPS Novgorodskaya str, 1, bld G, office 308 127247 Moscow - Russia info.dwtrru@dwgroup.com Tel.: +7 495 122 00 35 Fax: +7 495 122 00 36
- Germany** DAB PUMPEN DEUTSCHLAND GmbH Tackweg 110 - 47918 Tönisvorst - Germany info.germany@dwgroup.com Tel.: +49 2151 82136-0 Fax: +49 2151 82136-36
- Poland** DAB PUMPS POLAND SP. Z.O.O. Mokotów Marynarska ul. Postępu 15C 02-676 Warszawa - Poland Tel. +48 223 81 6065
- Ukraine** DAB UKRAINE Representative Office Regus Horizon Park 4M, Hrinchenka St, suit 147 03680 Kiev, UKRAINE info.ukraine@dwgroup.com Tel. +38 044 391 59 43
- China** DAB PUMPS CHINA No.40 Kaituo Road, Qingdao Economic & Technological Development Zone Qingdao City, Shandong Province, China PC: 266500 info.china@dwgroup.com Tel.: +8653286812030-6270 Fax: +8653286812210
- Hungary** DAB PRODUCTION HUNGARY KFT. H-8800 Nagykánizsa, Buda Ernő u.5 Hungary Tel. +36.93501700
- Mexico** DAB PUMPS DE MÉXICO, S.A. DE C.V. Av Gral Alvaro Obregón 270, oficina 355 Hipódromo, Cuauhtémoc 06100 México, D.F. Tel. +52 55 6719 0493



DAB PUMPS S.p.A.
Via M. Polo, 14 - 35035 Mezzano (PD) - Italy
Tel. +39 049 5125000 - Fax +39 049 5125950
www.dabpumps.com

11/16 ccd. 60160500



6 HOME PAGE

CONTRAST
MONITOR MENU
CT Contrast
Min 0 rpm Max 3,0 bar

LANGUAGE
MONITOR MENU
Language
LA ITA
ENG
FRE
0 rpm 3,0 bar

BACKLIGHT
MONITOR MENU
BK Backlight
Min 0 rpm Max 3,0 bar

7 SET POINT

SETPOINT MENU
Setpoint pressure
SP 3,0 bar
GO 2000 rpm 3,0 bar

9 PUMP ENABLE / DISABLE

TECH. ASS. MENU
AY Anti cycling
0 Disabled
GO 2000 rpm 3,0 bar

TECH. ASS. MENU
AY Anti cycling
1 Enable
GO 2000 rpm 3,0 bar

11

- Remove the top cover of the pump.
- Insert the pressure sensor into the designated port.
- Secure the sensor with the provided cap.
- Hand-tighten the cap.
- Connect the sensor to the pump's pressure tap.

8

INSTALLER MENU
RP Pressure fall to restart
P On 2,5 bar 0,5 bar
GO 2000 rpm 3,0 bar

SETPOINT MENU
Setpoint pressure
SP 3,0 bar
GO 2000 rpm 3,0 bar

TECH. ASS. MENU
AY Anti cycling
1 Enable
GO 2000 rpm 3,0 bar

10 ANTICYCLING

TECH. ASS. MENU
AY Anti cycling
0 Disabled
GO 2000 rpm 3,0 bar

TECH. ASS. MENU
AY Anti cycling
1 Enable
GO 2000 rpm 3,0 bar

12

13

Set Point default = 3 bar

$P.Air = SetPoint - 1 \text{ bar}$
(default = 3 - 1 = 2 bar)

14

40°C Max

4°C Min

50°C Max

0°C Min

www.dabpumps.com/e.sybox

product design award

2013